



372-3 Compact Meter



MODEL 372-3—Ohmmeter, 0.2 to 50 M Ω

Provides a wide range of resistance measurements in a small package. 0.2 ohm to 50 megohms. Especially useful for checking submersible pumps. Ideal for use in schools, on test benches or at incoming inspection facilities.

- **Ranges:** 0-500 Ω ; 0-5K Ω ; 0-50K Ω ; 0-500K Ω ; 0-5MEG Ω and 0-50 Meg Ω
- **Top Center Scale:** 5 Ω ; 50 Ω ; 500 Ω ; 5K Ω
- **Bottom Center Scale:** 30K Ω ; 300K Ω
- **Accuracy:** $\pm 3^\circ$ of Linear Arc Length
- **Includes:** Battery and Alligator Clip Leads



Range	Center (Ohms)	Maximum Current (Zero Ohms)	Maximum Voltage (Open Circuit)
RX1	5	340mA	1.5V
RX10	50	30mA	1.5V
RX100	500	3mA	1.5V
RX1000	5 K	0.3mA	1.5V
RX10K	30 K	0.65mA	21.5V
RX100K	300 K	65uA	21.5V

BATTERY REQUIRED:

1.5 "C", NEDA 14A (QTY: 1)

18V BATTERY ASSEMBLY (QTY: 1)

Efficient Customer Service has been a valuable tool for generations of Simpson customers. Customer Service offers ongoing support for our products and calibration and repair service for all current test equipment. To obtain service for a discontinued Simpson product, contact Customer Service for assistance. We offer information regarding our capabilities and referrals to other service centers.

Call (715) 588-3311

Ordering Information

COMPACT METER	Catalog No.	ACCESSORIES	Catalog No.
372-3 Ohmmeter	12311	Case, Brown Padded Polyester	00836
		Leads	00125
		18V Battery Assembly	00840

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Simpson:

12311