










SCALE 4:1

1. MATERIAL: HOUSING - 94V-0 RATED POLYCARBONATE CLEAR TERMINAL -
TERMINAL - 0.36 [.014] THICK PHORSPHOR BRONZE PLATED WITH 0.178 μm [.000007]
GOLD IN LOCALIZED AREA OVER 0.762 μm [.000030] PALLADIUM / NICKEL IN LOCALIZED
AREA, OVER 2.54 μm [.000100] THICK NICKEL ON ENTIRE TERMINAL.
WIRE HOLDER - POLYCARBONATE CLEAR.
SHIELD - BRASS DIN 17660 - CuZn33
2. DIMENSIONS ARE NOMINAL UNLESS OTHERWISE SPECIFIED.
3. PLUG WILL ACCEPT A 24-26 AWG STRANDED CONDUCTOR, PROVIDED THE INSULATION
CONDUCTOR DIAMETER IS WITHIN .89 - 1.09 [.035 - .043]; WITH THE SUM
OF DIAMETERS FOR ALL EIGHT CONDUCTORS WITHIN THE CABLE MUST NOT
EXCEED 7.8MM [.31 IN]. CABLE JACKET DIAMETER OF 6.0 - 7.0MM [.24 - .28 IN].
4. TERMINATED DIMENSION 6.15 [.242] MAXIMUM.
5. PACKAGE 1,000 ASSEMBLIES, 1,000 WIRE
HOLDERS, AND 1,000 SHIELDS.
6. PACKAGE 100 ASSEMBLIES, 100 WIRE HOLDERS,
AND 100 SHIELDS.
8. PACKAGE 500 ASSEMBLIES, 500 WIRE HOLDERS,
AND 500 SHIELDS.
9. MODULAR PLUG BOOT, PART NUMBER 1711510-X (X-DENOTES VARIOUS COLORS),
MAY BE USED WITH KIT ASSEMBLY SHOWN.
10. UL RECOGNIZED: FILE NUMBER E81956.

LOC		DIST		REVISIONS						
HM			00	P	LYR	DESCRIPTION	DATE	DWN	APVD	
					D1	REVISED PER ECO-11-005027	16MAR2011	RK	HMR	
					E	REV PER ECO-12-012918	16JUL2012	JM	JG	
					F	REV PER ECO-13-015339	04OCT2013	JB	JG	
					G	REV; ECO-14-004910	01APR2014	GG	JG	



SUPERSEDED BY: 5-1479184-3		7	5-1479184-4
		6	5-1479184-3
		8	5-1479184-2
		5	5-1479184-1
		PACKAGE	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN G. GARRETT 24JAN02	 TE Connectivity	
		CHK M. DELPHIAS 24JAN02		
DIMENSIONS: MME[INCHES]		APVD M. DELPHIAS 24JAN02	NAME	
		PRODUCT SPEC		KIT, 8 POSITION, MODULAR PLUG STRANDED WIRE, CATEGORY 6
		APPLICATION SPEC		
MATERIAL		114-13035	SIZE	CAGE CODE
FINISH		WEIGHT	DRAWING NO	RESTRICTED TO
		Customer Drawing	A100779C=1479184	-
		SCALE	8:1	SHEET 1 OF 1
		REV G		