

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0355070300](#)
Status: **Active**
Description: 2.00mm (.079") Pitch Sherlock™ Wire-to-Board Housing, Natural, 3 Circuits

Documents:

3D Model	Product Specification PS-35507-002 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-35507-001 (PDF)	

General

Product Family	Crimp Housings
Series	35507
Product Name	Sherlock™

Physical

Circuits (maximum)	3
Circuits Detail	3
Color - Resin	Natural
Flammability	94V-0
Gender	Female
Glow-Wire Compliant	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Polyester
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface (in)	0.079 In
Pitch - Mating Interface (mm)	2.00 mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +105°C


Electrical

CSA	LR19980
Current - Maximum	2A
UL	E29179

Material Info

Reference - Drawing Numbers

Product Specification	PS-35507-001
Product Specification	PS-35507-002
Product Specification	RPS-35507-003
Product Specification	RPS-35507-004
Product Specification	RPS-35507-005
Product Specification	RPS-35507-006
Product Specification	RPS-35507-011
Sales Drawing	SD-35507-001



Series image - Reference only

EU RoHS

**ELV and RoHS
Compliant**
REACH SVHC
Contains SVHC: No
**Halogen-Free
Status**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

[35507](#) Series

Mates With

Sherlock™ Wire-to-Board Header [35362](#) ,
[35363](#)

Use With

2.00mm (.079") Pitch Crimp Terminal [50212](#)
, [10440](#)