




MATERIAL NO.	ENG. NO.	STUD SIZE	"S" MAX	DESCRIPTION
192030470	B-S-137-08	8	.185/4.70	LOOSE
192030050	B-S-137-08T	8	.185/4.70	TAPE



PARTS ON TAPE

NOTE(S):

1. MATERIAL: STEEL
2. FINISH: NICKEL PLATED
3. WIRE SIZE: 16-14 AWG (1.5-2.5 MM²)
4. PART IS ROHS COMPLIANT.
5. AMBIENT OPERATING TEMPERATURE UP TO 900 °F (483 °C).

ADDED OPERATING TEMP EC NO: ETC2007-0297 DRW: JHEILE 2007/03/13 CHKD: JMACNEIL 2007/03/13 APPR: JMACNEIL 2007/03/14	QUALITY SYMBOLS ▽=0 ▽=0	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)				DIMENSION STYLE IN/MM		SCALE 4:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION		
			mm		INCH		DRAWN BY DMYRICK	DATE 2005/04/05	RING TONGUE TERMINAL, 16-14 AWG, KRIMPTITE, 900 DEG F (483 DEG C)				
			INCH		mm		CHECKED BY RDEROSS	DATE 2005/04/05					
			4 PLACES ± --- ± ---		3 PLACES ± --- ± .005		APPROVED BY RDEROSS		DATE 2005/04/05	MOLEX INCORPORATED			
			2 PLACES ± 0.13 ± .01		1 PLACE ± 0.25 ± ---		MATERIAL NO.		DOCUMENT NO.				SHEET NO.
			ANGULAR ±1/2°		SEE CHART		SD-19203-023		1 OF 1				
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE B		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						
			REV										

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19203-0050](#)