

PICCOLO PC D 65 T



Sample photo

Order symbol: PC D 65 T
Product nbr: 8724007
Description: Enclosure, PC
Remarks: Transparent cover

EAN: 6418074002105
El. number:
Finland: 3423509
Denmark: 8212001569
Italy: 7202030
Sweden: 2536844
Norway: 2536508

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

Dimensions:			Rating:
mm:	170	80	Ingress Protection (EN 60529): IP 66/67
inch:	6.7	3.1	Impact Resistance (EN 62262): IK 08
Materials:			Electrical insulation: Totally insulated
Material:	Polycarbonate		Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:	RAL 7035		UV resistance: UL 508
Cover colour:	Clear transparent		Flammability Rating (UL 746 C 5): UL 746C 5V
Cover screws material:	Polyamide		Glow Wire Test (IEC 695-2-1) °C: 960
Cover screws colour:	Grey		NEMA Class: NEMA 1, 4X, 6, 6P, 12, 13
Gasket material:	Polyurethane		Certificates:
Temperatures:			Germanischer Lloyd (GL)
Short term:	-40 ... 120 °C		Underwriters Laboratories
Continuous:	-40 ... 80 °C		Fimko
Short term:	-40 ... 250 °F		Europe EN 62208: 2003
Continuous:	-40 ... 175 °F		UL Canada
Accessories:			Gost R
D-MP	Mounting plate		
DH-3	DIN-35 Mounting rail		
FP 22040	Wall fastening lug (2 pcs)		

PICCOLO 170x80x65-85

