

SPECIFICATIONS



RESISTANCE RANGE	100 TO 100K OHMS
RESISTANCE TOLERANCE	±5%
ACCURACY	±0.35% OF VOLTAGE RATIO
REPEATABILITY	±0.02% OR RESOLUTION OF POT
RESOLUTION	SEE POT SPECIFICATIONS
POWER RATING	2 WATTS
OPERATING TEMPERATURE	-30°C TO +85°C
TEMPERATURE COEFFICIENT	±20 PPM/°C
TURNS	10 (000 TO 999 COUNTS)
TERMINALS	GOLD PLATED LUGS
HOUSING MATERIAL	HIGH TEMP. BLACK PLASTIC


REV.	BY	DATE	PART NO.
A	BT	1-16-93	ADDED SPECIFICATIONS
B	AT	2-20-02	ADDED 1 TURN POTENTIOMETER

NOTES:

- 1. USE ETI SYSTEMS POTENTIOMETERS MODEL MW22B.
- 2. POTENTIOMETERS MAY BE 1,3,5,10 TURNS.
ALSO MULTIPLE GANGS.
- 3. DIAL AVAILABLE WITHOUT POT, ASK FOR DA10N
- 4. THREADS WILL ACCEPT PANEL THICKNESS OF 3/16 MAX.
- 5. SEE POTENTIOMETER CATALOG FOR ADDITIONAL SPECIFICATIONS.

*MODEL WITH MW20B IS DW20.



	SCALE	NONE	THIS DOCUMENT CONTAINS PROPRIETARY DATA OF POLARIS INDUSTRIAL ENTERPRISES, INC. NO DISCLOSURE, REPRODUCTION, OR USE OF ANY PART THERE OF MAY BE MADE EXCEPT BY WRITTEN PERMISSION.	 CARLSBAD CALIFORNIA
	DATE:	5-8-87		
	BY			
<u>TOLERANCES</u> XX = +/- .010" FRACT. = +/- 1/64" XXX = +/- .005" ANGLES = +/- 1/2° ALL SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE.	APPRV'D	BT	<u>TITLE</u> POT/DIAL COMBINATION	<u>PART NO.</u> DW22
	CODE IDENT: 19477			