

## Fluorescent and Flexible-Neck Lights

# A few more bright ideas from Black Box.



### FEATURES

- » **Fluorescent Lights**
- » **Cool, energy-efficient 13-watt illumination.**
- » **Multiposition hanger hook rotates 360 degrees.**
- » **Full-length reflectors provide light output equal to a 60-watt incandescent bulb.**

### **Magnetic Flexible-Neck Trouble Light**

- » **Directs light exactly where you want it.**
- » **A powerful magnet holds the Light in place.**
- » **UL® Listed.**

### Fluorescent Lights

These rugged, heavy-duty fluorescent utility lights feature cool, energy-efficient 13-watt fluorescent lamps. Full-length reflectors provide light output equivalent to 60-watt incandescent bulbs.

These standard-size, powerful utility lights are safe to handle with no danger of burns. Molded multiposition hanger hooks make it easy to manipulate the light source.

Premium-quality construction features include shatter-resistant outer housings, three-conductor plug-in ballasts, and easy push button on/off switches.

All electrical components are sealed for user safety, and power cords are UL® Listed. The EPL105 comes with a 25-foot line cord and the EPL110 has 40 feet of oil-resistant line cord with a heavy-duty power take-up reel.

An optional magnetic clamp provides easy wall or ceiling mounting. These 20" x 2" lights meet OSHA standards and come with one-year warranties.

### **Magnetic Flexible-Neck Trouble Light**

These flexible-neck trouble lights have a powerful magnet that holds them exactly where you need them. They come with a 25' cord and are UL® Listed.

| Item                                   | Code   |
|----------------------------------------|--------|
| Fluorescent Utility Light, 25-ft. Cord | EPL105 |
| Fluorescent Reel Light, 40-ft. Cord    | EPL110 |
| Magnetic Flexible-Neck Trouble Light   | EPL100 |