

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT — By —

ALL RIGHTS RESERVED.

LOC

J

DIST

—

REVISIONS

変更

P

LTR

DESCRIPTION

DATE

DWN

APVD

F

REVISED

ECR-14-018500

18DEC2014

TS

YF

WIRE RANGE ID MARK
("M" SIZE MARK)
(STAMPED ON BOTTOM)

端子識別マーク "M"
(底面に刻印)

C

C

2.5

0.5

1.4

1

2.6

16±0.5

7

0.8

2.6±0.3

1.6±0.3

1.2

4

5

5MIN

A

B

A

B

断面 C-C

SECT C-C

2

4

断面 A-A

SECT A-A

3±0.4

3.3±0.4

断面 B-B

SECT B-B

5±0.4

4.7±0.4

断面 A-A

SECT A-A

(175027のみ適用)
(ONLY 175027)

2.8±0.4

3.4REF

断面 B-B

SECT B-B

(175027のみ適用)
(ONLY 175027)

3.8±0.4

4.8REF

1 製品規格 ; 108-5216, 108-5231, 108-5264, 108-3371

2 部分金めっき

3. 取付適用規格 ; 114-5091

4 識別用金めっき (全周)

5 部分金めっき (両側のみ)

1. SPEC; 108-5216, 108-5231, 108-5264, 108-3371

2 SELECTIVE GOLD PLATING

3. APPLICATION SPEC; 114-5091

4 GOLD PLATING FOR DISCERNMENT (ALL AROUND)

5 SELECTIVE GOLD PLATING (ONLY BOTH SIDES OF THE BOX)

WIRE RANGE

0.5~1.25mm²
(AWG#20-#16)

INSULATION DIA.

2~2.6mmφ

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
単位 : 耗
mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
一般公差

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

MATERIAL
材料

SEE TABLE

FINISH
仕上

SEE TABLE

DWN

12MAY06

M.SUGAWARA

CHK

12MAY06

T.SHINOHARA

APVD

12MAY06

K.BETSUI

PRODUCT SPEC

製品規格

SEE NOTE 1

APPLICATION SPEC

取付適用規格

SEE NOTE 3

WEIGHT

—

CUSTOMER DRAWING

SCALE

5:1

SHEET

1 OF 1

REV

F

070 SERIES RECEPTACLE CONTACT

SIZE

A3

CAGE CODE

00779

DRAWING NO

番号

C=173631

RESTRICTED TO

—

	5 2 部分金めっき SELECTIVE GOLD	黄銅 板厚0.3 BRASS t0.3	1-173631-2
SEE DRAWING 173631-8			173631-8
175027-7	4 2 部分金めっき SELECTIVE GOLD	リン青銅 板厚0.3 PHOS BRO. t0.3	173631-7
175027-6	錫めっき済み PRE-TINNED	銅合金 板厚0.3 COPPER ALLOY t0.3	173631-6
175027-2	4 2 部分金めっき SELECTIVE GOLD	黄銅 板厚0.3 BRASS t0.3	173631-2
175027-1	錫めっき済み PRE-TINNED	黄銅 板厚0.3 BRASS t0.3	173631-1
バラ端子型番 L/P. NUMBER	仕上 FINISH	材料 MATERIAL	型番 PART NUMBER

1470-19 (3/11)