

MNX ABS 150/75 HG



Order symbol: ABS 150/75 HG
Product nbr: 6081314
Description: Enclosure, ABS
Remarks: Grey cover

EAN: 6418074022943
El. number:
 Finland 3420553
 Denmark 8212023275
 Italy 7361095
 Sweden 2535754

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Sample photo

Dimensions:		L	W	H	Rating:
mm:		180	130	75	Electrical insulation: Totally insulated Halogen free (DIN/VDE 0472, Part 815): Yes Flammability Rating (UL 746 C 5): UL 94 HB Glow Wire Test (IEC 695-2-1) °C: 650 NEMA Class: NEMA 1, 4, 4X, 6 Ingress Protection (EN 60529): IP 66/67 Impact Resistance (EN 50102): IK 07
inch:		7.1	5.1	3	
Materials:					
Material:	ABS				
Gasket material:	TPE				
Base colour:	RAL 7035				
Cover colour:	RAL 7035				
Cover screws material:	Polyamide				
Cover screws colour:	Grey				
Temperatures:					
Short term:	-40 ... 80 °C				
Continuous:	-40 ... 60 °C				
Short term:	-40 ... 175 °F				
Continuous:	-40 ... 140 °F				
Accessories:					
MIV 150	Mounting plate (Galvanized steel)				
MIN 10	DIN-15 Mounting rail				
MIN 15	DIN-15 Mounting rail				
MIV 10	DIN-35 Mounting rail				
MIV 15	DIN-35 Mounting rail				
FP A 150/180	Front plate (Aluminium)				
HFP 180	Front plate hinge series (2 pcs)				
FP 22046	Wall fastening lug (4 pcs)				

