


Item no.: 713-1423

Product description: Male header (for PCBs) Angled solder pin 0.8 x 0.8 mm 3x2-pole Pin spacing 3.5 mm / 0.138 in 100% protected against mismatching 2 rows Horizontal PCB mounting



Produkt kann von Bild abweichen / product may differ

Packing unit 100 pieces

RoHS compliant

Weight	1.9 g
Color	black
pole count	6
Height	13.3 mm
Height	0.524 in
Width	12 mm
Width	0.472 in
Depth	13.5 mm
Depth	0.531 in
Pin spacing from	3.5 mm
Pin spacing from	0.138 in
Rating based on	IEC/EN 60664-1
Overvoltage category EN I	III
Pollution degree	2
Measured voltage EN	160 V
Measured shock voltage	2.5 kV
Current intensity EN	10 A
Overvoltage category EN II	II

Pollution degree	2
Measured voltage EN	250 V
Measured shock voltage	2.5 kV
Current intensity EN	10 A



Overvoltage category EN III	III
Degree of pollution	3
Rated voltage EN	80 V
Rated surge voltage	2.5 kV
Nominal current	10 A
Solder pin length [mm]	3.8 mm
Solder pin width A [mm]	0.8 mm
Solder pin width B [mm]	0.8 mm
Diameter of drilled hole [mm]	1.2 mm
Tolerance of drilled hole diameter [mm]	0.1 mm
Material group	I
Temperature stability	-60 °C to +115 °C
Flammability category, based on UL 94	0V
Contact material	Electrolytic copper (Ecu)
Contact plating	tin-plated
Customs Tariff No.	85369010
Country of Origin	Deutschland

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected