


# PC SCREW TERMINALS

## LOW PROFILE VERTICAL TYPE



7778-7


- Color coded screws available (add color screw suffix to Cat. No.)



### SPECIFICATIONS

**Rated:** 15 Amps  
**Terminal:** .032 (.81) Brass, Matte Tin Plate  
**Binding Head Screw:** Brass, Nickel Plate


#### Mounting Detail



**CAT. NO. 7784** (No Screw Supplied)

**CAT. NO. 8198** (Screw Supplied Unassembled)


**CAT. NO. 7778** (Screw Installed & Captivated)



7775-2

- Color coded screws available (add color screw suffix to Cat. No.)

#### Mounting Detail



**CAT. NO. 7785** (No Screw Supplied)

**CAT. NO. 8195** (Screw Supplied Unassembled)

**CAT. NO. 7775** (Screw Installed & Captivated)

## VERTICAL TYPE


### EXTENDED



7699-6

#### PC MOUNT


- Color coded screws available (add color screw suffix to Cat. No.)



### SPECIFICATIONS

**Rated:** 15 Amps  
**Terminal:** .032 (.81) Brass, Matte Tin Plate  
**Binding Head Screw:** Brass, Nickel Plate

#### Mounting Detail



**CAT. NO. 7789** (No Screw Supplied)

**CAT. NO. 7697** (Screw Supplied Unassembled)



**CAT. NO. 7699** (Screw Installed & Captivated)

### HEAVY DUTY



8174

#### Mounting Detail



**CAT. NO. 7791** (No Screw Supplied)

**CAT. NO. 8174** (Screw Supplied Unassembled)

## 30 AMP - VERTICAL


### PRINCIPAL FEATURES

- Compact, heavy duty design
- Six snap-in legs for total stability
- Serrated top surface secures connection




8199-6

- Combination drive, binding head screw
- Color coded screws available (add color screw suffix to Cat. No.)



#### Mounting Detail



### SPECIFICATIONS

**Rated:** 30 Amps  
**Terminal:** .032 (.81) Brass, Matte Tin Plate  
**Binding Head Screw:** Brass, Nickel Plate

**CAT. NO. 7786** (No Screw Supplied)

**CAT. NO. 8197** (Screw Supplied Unassembled)


**CAT. NO. 8199** (Screw Installed & Captivated)

### HEAVY DUTY



8196

#### Mounting Detail




### SPECIFICATIONS

**Rated:** 30 Amps  
**Terminal:** .045 (1.14) Brass, Matte Tin Plate  
**Screw:** Stainless Steel

**CAT. NO. 7787** (No Screw Supplied)

**CAT. NO. 8196** (Screw Supplied Unassembled)

## COLOR CODED SCREW TERMINAL SELECTION GUIDE



### Color Coded Screw Terminals provide:

- Quick identification
- Visibility for field service troubleshooting

### SPECIFICATIONS

#### Combination Binding Head:

Standard screw is Brass, Nickel Plate. For painted, color head, add suffix as shown.



**COLOR SELECTION:**  
 Select desired screw terminal and add color suffix to the screw terminal Cat. No.

| HEAD COLOR | SUFFIX |
|------------|--------|
| RED        | -2     |
| BLACK      | -3     |
| WHITE      | -4     |
| BLUE       | -5     |
| GREEN      | -6     |
| YELLOW     | -7     |
| NICKEL     | none   |

**CAT. NO. COLOR SUFFIX**  
 Ex: XXXX -X



Refer to page 133 for color screws only