




Right Angle DIN Plugs


171-1051-EX, 171-1080-EX

KOBI CONN

Right Angle DIN Plugs



5 Pin
180 Arc
171-1051-EX



8 Pin
270 Arc
171-1080-EX

Dimensions: (in.) mm

SPECIFICATIONS

Type:	Right Angle DIN
Insulation Resistance:	100MΩ min @ 500VDC
Contact Resistance:	30mΩ max
Dielectric Strength:	250VAC for 1 Minute
RoHS Compliant by Exemption	

MATERIALS

Color:	171-1051-EX - Gray, 171-1080-EX - Black
Sleeve:	Nickel Plated Steel
Body:	Polyethylene
Strain Relief:	PVC
Insulator:	ABS
Pins:	Nickel Plated Brass

Date Last Revised: 4-21-10

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

KC-301381

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

171-1051-EX, 171-1080-EX

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[171-1080-EX](#) [171-1051-EX](#)