



Search Results

- Evaluate
- FAQ's
- How to Buy
- Bill of Material
 - Favorite Products List
 - Locate Distributor

[Home](#) > [Products Overview](#) > [Search Results](#) >

Current refinements (click to remove) [Search Tips](#) Within Results

Text Search: 'F9D6P-6JM1Y'

Your search criteria matched only one product, shown below

F9D6P-6JM1Y



- Pass all TIA/EIA-568-B.3 performance requirements
- 100% factory inspected end face geometry in compliance with Telcordia GR -326-CORE, Issue 3
- Typical insertion loss per connection: 0.25dB
- UPC polished (55dB minimum return loss)
- Factory terminated and 100% tested for insertion loss and return loss
- Insertion loss and return loss data recorded for every singlemode patch cord
- Lifetime traceability of test data to a Q.C. number on each patch cord
- Highest quality flame retardant fiber optic cable with tight -buffered coating on each optical fiber

	Part Number	F9D6P6JM1Y
	RoHS Compliancy Status	Compliant
	Note	F9D6P6JM1Y replaces F9D6P6JM1
	Part Description	FJ® Plug to F® Jack Module singlemode duplex patch cord (one F® Plug on one end and one FJ® Jack Module on the other end)– 9/125µm.
	Product Type	FJ® Patch Cords
	Length (m)	1
	Fiber Compatibility	9/125µm
	Fiber Cable Size	3mm
	Fiber Cable Type	Jacketed
	Fiber Type	Singlemode
	Connector 1 Type	FJ® Plug
	Connector 2 Type	FJ® Jack Module
	End Configurations	FJ® Plug to F® Jack
	Fiber Count	2
	Flammability Rating	Riser (OFNR)
	Pricing Description	PC FJ Plug To FJ Jackµm Dupl 1m
	Min. Order UOM	PC
	Min. Order Qty.	1
	BOM Qty. (# of Pkgs.)	0
	Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.