




Isolierkörpermaterial
PBT, UL94V-0

Kontaktmaterial
Messing

Kontaktoberfläche
Ni, Sn

Kontaktwiderstand
20mΩ max

Isolationswiderstand
1000MΩ min

Strombelastbarkeit
3A

Betriebstemperatur
-40°C - +105°C

Betriebsspannung
250V AC

Prüfspannung
500V AC

Verpackung
Blisterverpackung

Insulator material
PBT, UL94V-0

Contact material
Brass

Plating
Ni, Sn

Contact resistance
20mΩ max

Insulation resistance
1000MΩ min

Current rating
3A


Operating temperature
-40°C to +105°C

Operating voltage
250V AC

Test voltage
500V AC

Packing
Tray packing

Dimensions		
No. of contacts	A	B
10	17.48	10.16
14	22.56	15.24
16	25.10	17.78
20	30.18	22.87
26	37.80	30.48
34	47.96	40.64
40	55.58	48.26
50	68.28	60.96
60	80.98	73.66
64	86.06	78.74



Bestellcode / Ordercode

Polzahl

10 / 14 / 16 / 20 /
26 / 34 / 40 / 50 / 60 / 64

No. of contacts

10 / 14 / 16 / 20 /
26 / 34 / 40 / 50 / 60 / 64

AWLP xx / 3,2 T

Bitte „x“ durch die geeignete Option ersetzen
Please replace „x“ with appropriate option