


The copying, distribution and utilisation of this document as well as the communication of the contents to others without expressed authorization is prohibited according to §18 UWG German Law. Offenders will be held liable for the payment of damages according to §19 UWG German Law. All rights reserved. In particular the right to carry out patent, utility model or ornamental design registrations.

Mechanical data (according to IEC 61076-2-101)		Material	
no. of poles / coding	4 / T	contacts / surface	CuZn / Au
contact termination	dip solder / pin	contact carrier	PA4T
contact-Ø	4xØ1.5mm	colour	black
temperature range	-40 °C / +105 °C	sealing gasket	FKM
protection class	IP 67		
mating cycles	>100		

further information:
- see technical data M12-4




All specified data refers to the mounted M12 installation plugs $\geq$ IP54 and requires that the connector pair be correctly plugged and locked. Influences from wires, cables or PCB mounting are also to be taken into consideration.

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts gem §18 UWG verboten. soweit nicht ausdrücklich gestattet. Zuwiderhandlungen verpflichten zu Schadenersatz (§19 UWG). Alle Rechte vorbehalten, insbesondere das Recht, Patent-, Gebrauchsmuster- oder Geschmacksmusteranmeldungen durchzuführen. CONINVERS GmbH Heisenbergstrasse 1 D-71083 Herrenberg

drilling plan

component side (front view PC-Board)



general tolerance acc. to DIN ISO 2768-c			technical changes reserved	Index 2 / 2013-03-05	scale: 2:1
design	date	name	Series DSIV M12-pin-contact carrier 4pole pin/T-coding/straight		
chk.	2012-10-25	Thumm			
			order-no.:	1406396	
			article designation:	SACC-CI-M12MST-4CON-L180 THR	
			doc.-no.:	00689842	