


NOTES: UNLESS OTHERWISE SPECIFIED

1. P/N: XB2ACOLOR
HOUSING : MOLDED NYLON TYPE 6,6. AVAILABLE IN BLACK, RED, YELLOW.
KNOB: MOLDED PLASTIC. AVAILABLE IN BLACK, RED, YELLOW.
NEEDLES: SPRING TEMPER MUSIC WIRE. TIN PLATED.
NEEDLE CLUSTER HOUSING: BRASS. TIN PLATED
CLAMPING SCREW: STAINLESS STEEL.

2. P/N: 9306COLOR
HOUSING: MOLDED NYLON 6,6. AVAILABLE IN BLACK, RED, YELLOW.
SOCKET & BANANA PLUG: BRASS. NICKEL PLATED.
CONTACT: BeCu OR PHOSPHOR BRONZE. NICKEL PLATED.
HARDWARE: BRASS EYELET. COPPER FINISH, TIN PLATED
TERMINAL RING.

3. P/N: W-600/COLOR
18AWG 65X36 TINNED COPPER
0.144 [3.66] O.D. PVC INSULATION
AVAILABLE IN TEN COLORS.

3. PERFORMANCE
MAXIMUM CURRENT: 500 MILLIAMPS
MAXIMUM VOLTAGE: <33 V AC < 70 V DC
MAXIMUM TEMPERATURE: 221°F (105°C)



		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ANGLES		CONTRACT NO.	
		± .XX ±	±	APPROVALS	DATE
		± .XXX ±	±	DRAWN	11/11
		MATERIAL SEE NOTE.		APPROVED BY	
		FINISH			
		SEE NOTE.			
NEXT ASSY	USED ON				
APPLICATION		DO NOT SCALE DRAWING			
				DESCRIPTION	
				E-Z-HOOK® DIVISION OF TEKTEST INC. ARCADIA, CA 91006 U.S.A.	
				INSULATION PIERCING XB TO STK SHRD R/A STD BAN PLUG	
				SIZE CODE IDENT NO. DRAWING NO.	
				A 08505 636XB	
				SCALE 1:1 SHEET 1 OF 1	