


Ripac ECO 3 U, 6 U, sheet steel



Material/surface finish:

Side panels:
1.5 mm sheet steel, zinc-plated,
passivated
Flanges/horizontal rails:
Extruded aluminium section,
clear-chromated

Supply includes:

Side panels, flanges,
horizontal rails, threaded inserts

Detailed parts lists,

see page 1155.

Tests:


Vibration and shock-tested to:
IEC 600-68-2-6 test Fc
IEC 600-68-2-27 test Ea

Standards:

Ripac subracks are based
on the system dimensions of
IEC 60 297-3/-5.

Detailed drawing,

see page 1155.



1 for backplane

2 for backplane

					Model No. RP		Page
					1	2	
U (H1)					3	6	
B1 mm	B2 HP	Side panel (T1) mm	T2 mm	Max. PCB depth mm	For backplane	For backplane	
482.6 (19")	84	175	150	160	3688.114	3688.116	
		235	210	220	3688.115	3688.117	
Accessories							
Trim section rear, 3 U					3688.112		497
Trim section rear, 6 U					3688.113		497
Z (connector) rail					3684.602		504
Insulating strips					3684.611		505
Cover, perforated, for 175 mm depth					3688.105		518
Cover, perforated, for 210 mm depth					3688.106		518
Cover, solid, for 175 mm depth					3688.107		518
Cover, solid, for 210 mm depth					3688.108		518
Mounting clips for covers					3688.109		518
Assembly screw for mounting clips					9902.188		518
Guide rails							509
Horizontal rails							498