





Amp	Volt	Hz	IP Ident. colour + h	 Part No.	Plugs and sockets for extra-low voltages up to 50 V	2 pole IEC/EN 60 309	  g	EAN No. 4015609...																													
16	24~	50/60	-	10 400	panel sockets straight, flange dimension 50 x 50     fixing hole fixing dimension = a + b, flange dim. = d + e <table><tr><th>Ampère</th><th>a</th><th>b</th><th>c</th><th>d</th><th>e</th><th>f</th><th>h</th><th>n</th><th>p</th></tr><tr><td>16 A</td><td>41</td><td>41</td><td>4,2</td><td>50</td><td>50</td><td>42</td><td>40</td><td>18</td><td>4</td></tr><tr><td>32 A</td><td>41</td><td>41</td><td>4,2</td><td>50</td><td>50</td><td>42</td><td>40</td><td>18</td><td>4</td></tr></table>	Ampère	a	b	c	d	e	f	h	n	p	16 A	41	41	4,2	50	50	42	40	18	4	32 A	41	41	4,2	50	50	42	40	18	4		
	Ampère	a	b	c		d	e	f	h	n	p																										
	16 A	41	41	4,2		50	50	42	40	18	4																										
	32 A	41	41	4,2		50	50	42	40	18	4																										
	42~	50/60	12	10 401																																	
	42~	100/200	4	10 402																																	
	42~	300	2	10 403																																	
42~	400	3	10 404																																		
42~	>400/500	11	10 405																																		
42 ~	-	10	10 406																																		
32	24~	50/60	-	11 400																																	
	42~	50/60	12	11 401																																	
	42~	100/200	4	11 402																																	
	42~	300	2	11 403																																	
	42~	400	3	11 404																																	
	42~	>400/500	11	11 405																																	
	42 ~	-	10	11 406																																	

10	101								
10	101								

004928	004935	004942	004959	004966	004973	004980	006977	006984	006991	007004	007011	007028	007035
--------	--------	--------	--------	--------	--------	--------	--------	--------	--------	--------	--------	--------	--------