


LOC				REVISONS			
G	14	P	#	ZONE	LTR	DESCRIPTION	DATE
				C		REVISED PER 0720-0230-93	2/20/94

METRIC

DIMENSIONS LISTED IN mm [INCHES]

WIRE RANGE		E13288 Listed	
22-16 AWG STRANDED		22-16 AWG STRANDED	
LR7189 Certified		MILITARY P/N AND CLASS	
NOT CERTIFIED		NOT APPLICABLE	

1 STAMP AMP 22-18* APPROX AS SHOWN
22-16 TERMINALS ARE STAMPED 22-18 IN
ACCORDANCE WITH MILITARY SPECIFICATION
MIL-T-7928, COMMERCIAL WIRE RANGE IS 22-16



AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111
FOR ORDER ENTRY	1-800-526-5142

MAX RECOMMENDED OPERATING TEMPERATURE:	170°C MAX
VOLTAGE RATING:	NOT APPLICABLE
WIRE CROSS SECTIONAL AREA RANGE:	0.26-1.65mm² [509-3,260] CIR MILS STRANDED

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLG DEC ± .1 3 PLG DEC ± .1 ANGLES MATERIAL COPPER PER ASTM B-152 ANNEALED	FINISH TIN PLATE 0.00254 [1.000100] MIN THK PER MIL-T-10727
--	--

DR 2-2-93 TA BRILKMAN	CHK 2-2-93 DA PATTERSON
APPO 2-2-93 DE MILLER	APPO 2-2-93 JL NECKLEY

NAME	AMP	AMP Incorporated Harrisburg, PA 17105-3608
------	-----	---

APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO
WEIGHT	SCALE 10:1	00779	C-320677

TERMINAL, RING TONGUE,
BUDGET

320677
PART NO