



GK14M

Rigid stem hooded exposed tip probe



Copyright © 2007 Test Products International, Inc.

Application

Exposed junction for fast response
in air applications.

Range°F°C

-58° to 500°F
-50° to 250°C

Probe tip

44

Dimensions

Stem Length: 3.74" (95mm)
Diameter: 0.13" (3.2mm)
Lead Length: 39.4" (1M)

Insulation Material

Polyurethane