



D

C

B

A



SECTION A-A

△4	OBSOLETE	-	43	6.552	6.872	7.307	7.012	.437	7.557	8-530654-3
△4	OBSOLETE	-	28	4.212	4.532	4.967	4.672	.370	5.217	8-530654-2
△4	OBSOLETE	-	36	5.460	5.780	6.215	5.920	.437	6.465	8-530654-0
△4		-	30	4.524	4.844	5.279	4.984	.437	5.529	7-530654-9
△4	OBSOLETE	-	24	3.588	3.908	4.343	4.048	.370	4.593	7-530654-7
△4		-	22	3.276	3.596	4.031	3.736	.370	4.281	7-530654-6
△4		-	18	2.652	2.972	3.407	3.112	.370	3.657	7-530654-5
△4		-	15	2.184	2.504	2.939	2.644	.370	3.189	7-530654-4
△4		-	10	1.404	1.724	2.159	1.864	.370	2.409	7-530654-2
△4	OBSOLETE	-	6	.780	1.100	1.535	1.240	.370	1.785	7-530654-1
	1-530654-3	-	43	6.552	6.872	7.307	7.012	.437	7.557	3-530654-3
	1-530654-2	-	28	4.212	4.532	4.967	4.672	.370	5.217	3-530654-2
	1-530654-1	-	44	6.708	7.028	7.463	7.168	.437	7.713	3-530654-1
	1-530654-0	-	36	5.460	5.780	6.215	5.920	.437	6.465	3-530654-0
	530654-9	-	30	4.524	4.844	5.279	4.984	.437	5.529	2-530654-9
	530654-8	-	25	3.744	4.064	4.499	4.204	.370	4.749	2-530654-8
	530654-7	-	24	3.588	3.908	4.343	4.048	.370	4.593	2-530654-7
	530654-6	-	22	3.276	3.596	4.031	3.736	.370	4.281	2-530654-6
	530654-5	-	18	2.652	2.972	3.407	3.112	.370	3.657	2-530654-5
	530654-4	-	15	2.184	2.504	2.939	2.644	.370	3.189	2-530654-4
	530654-3	-	12	1.716	2.036	2.471	2.176	.370	2.721	2-530654-3
	530654-2	-	10	1.404	1.724	2.159	1.864	.370	2.409	2-530654-2
	530654-1	-	6	.780	1.100	1.535	1.240	.370	1.785	2-530654-1
△1	PART NO	NO.OF. POSITION	A	B	C	D	W	F	△2	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 19MAR75	TE Connectivity	
DIMENSIONS: INCHES		CHK 01NOV80	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 01NOV80	PRODUCT SPEC	
0. PLC ± -		APPLICATION SPEC		
1. PLC ± -		SIZE		
2. PLC ± .005		CAGE CODE		
3. PLC ± .005		DRAWING NO		
4. PLC ± -		RESTRICTED TO		
ANGLES		A100779530654		
FINISH		CUSTOMER DRAWING		
MATERIAL SEE CALL-OUT		SCALE 4:1 SHEET 1 OF 1 REV N2		
SEE NOTES				