



Quality Products. Service Excellence.


Audio Sound Distribution Line Matching *119 Series*



Features

- Suitable for driving from solid state amplifiers where isolated windings are not required or can be used with our "Classic" 1600 tube output transformers to provide a 25V or 70V line output.
- 8 or 16 ohm input, 25V or 70V line output.
- Frequency response 50 Hz. to 10 Khz. at full ratings
- Leads 6" long minimum
- Can be reversed for operation at high power speaker locations.
- For speaker matching from older "Classic" 600 Ohm equipment - check out our **119DA** matching transformer.

Gallery



	Max Output	Line	Mounting	Mounting	Mounting	Wt.	Drawing	Overall Dimensions						
Part No.	(Watts)	Output	Type	Centers	Hole	Slot	G	(lbs.)	Figure	A	B	C	D	E
119Y30	30	70 & 25v	Bracket	3.56	0.19			2.40	1.00	4.03	2.25	2.63	3.56	-
119Y60	60	70 & 25v	X Mtg.	2.00 x 2.19	0.20 x 0.38			3.30	2.00	2.50	3.25	3.06	2.00	2.19
119Y100	100	70v only	X Mtg.	2.50 x 2.19	0.20 x 0.38			4.70	2.00	3.13	3.50	3.81	2.50	2.19
119Y250	250	70v only	X Mtg.	2.50 x 2.94	0.20 x 0.38			6.70	2.00	3.13	4.25	3.81	2.50	2.94

Data subject to change without notice