


THIS DOCUMENT CONTAINS DATA PROPRIETARY
TO PROJECTS UNLIMITED, INC. ANY USE OR
REPRODUCTION, IN ANY FORM, WITHOUT PRIOR
WRITTEN PERMISSION OF PROJECTS UNLIMITED, INC.
IS PROHIBITED.
© 2005, Projects Unlimited Inc.

SPECIFICATIONS

PARAMETERS	VALUES	UNITS
RATED VOLTAGE	10	V _{p-p}
OPERATING VOLTAGE RANGE	1 ~ 30	V _{p-p}
RATED CURRENT (MAX)	7	mA
CAPACITANCE	15,500	pF
MINIMUM SPL @ 10 CM	86	dBA
RESONANT FREQUENCY	3,000±500	Hz
OPERATING TEMPERATURE	-20 ~ +70	°C
STORAGE TEMPERATURE	-30 ~ +80	°C
HOUSING MATERIAL	RYTON-R10 BLUE	—
TERMINAL MATERIAL		—
WEIGHT	3	grams

REVISIONS			
LTR	DESCRIPTION	DATE	APPROVED
—	RELEASED FROM ENGINEERING	5/20/02	
A	REVISED TO NEW TEMPLATE, UPDATED SPECS. & DIMS.	8/11/05	



NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS.
2. SPECIFICATION SUBJECT TO CHANGE
OR WITHDRAWAL WITHOUT NOTICE.

FILE NAME
SMT2118.DWG

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN
MILLIMETERS, TOLERANCES ARE ± 0.5 AND
ANGLES ARE $\pm 3^\circ$.

APPROVALS	DATE
DRAWN RABL	05/02
CHECKED X.X.	X/XX
APPROVED S.J.	6/4/02
DO NOT SCALE DRAWING	

projects ®
unlimited

Dayton, Ohio

TRANSDUCER (PIEZO)

SIZE A
DRAWING NO.
SMT-2118

SCALE: N.T.S. SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[PUI Audio:](#)

[SMT-2118](#)