

Aven Inc.
4595 Platt Rd.
Ann Arbor, MI 48108
Phone: 734.973.0099
Email: info@aventools.com • Web Address: www.aventools.com

All Categories > Ergo Stainless Steel Cutters > Stainless Steel Cutters > Stainless Steel Pliers > Niptec Cutters > Specialty Cutters > Parallel Action Pliers > Item # 10764



[larger image](#)

Item # 10764, Flat Nose Plier With Wire Cutter and Plastic Grip

8" Parallel Action Pliers with Wire Cutters

- Serrated Jaws with V-Slot
- Maximum Jaw Opening: 17mm (0.7")
- Soft Wire Cutting Capacity: 6mm (0.24")
- Overall Length: 203mm (8")
- Jaw Length: 41mm (1.6")
- Jaw Width: 12.5mm (1.4")

Specifications

Maximum Jaw Opening	0.7 in 17 mm
Cutting Capacity	0.24 in 6 mm
Overall Length	8 in 203 mm
Jaw Length	1.6 in 41 mm
Jaw Width	1.4 in 12.5 mm
Weight	1.20 lb

[Print](#) [Back](#)