

USB and BI-DIRECTIONAL CABLES



Fig.1



Fig.2



Fig.3



Fig.4



Fig.5



Fig.6



Fig.7



Fig.8



Fig.9

USB to USB Cables

Retail Part No.	Bulk Part No.	Figure No.(s)	Description	Length Ft. (m)	Color	Cable	Speed
66-1120		1	USB-A (Male) to USB-A (Male) USB 2.0	6.5 (2)	Black	1 Pair x 26 AWG, 2 x 20 AWG	480Mbps
45-1413		1 & 2	USB-A (Male) to USB-B (Male) USB 1.0	3.3 (1)	Putty	1 Pair x 26 AWG, 2 x 20 AWG	480Mbps
45-1416		1 & 2	USB-A (Male) to USB-B (Male) USB 1.0	6.5 (2)	Gray	1 Pair x 26 AWG, 2 x 20 AWG	480Mbps
45-1403		1 & 2	USB-A (Male) to USB-B (Male) USB 1.0	9.9 (3)	White	1 Pair x 26 AWG, 2 x 20 AWG	480Mbps
45-1406		1 & 2	USB-A (Male) to USB-B (Male) USB 1.0	13.2 (4)	Putty	1 Pair x 26 AWG, 2 x 20 AWG	480Mbps
45-1410		1 & 2	USB-A (Male) to USB-B (Male) USB 1.0	16.5 (5)	Putty	1 Pair x 26 AWG, 2 x 20 AWG	480Mbps
66-1126		1 & 2	USB-A (Male) to USB-B (Male) USB 2.0	16.5 (5)	Black	1 Pair x 26 AWG, 2 x 20 AWG	480Mbps
66-1121		1 & 2	USB-A (Male) to USB-B (Male) USB 2.0	6.5 (2)	Black	1 Pair x 26 AWG, 2 x 20 AWG	480Mbps
66-1125		1	USB-A (Male) to USB-A (Male) USB 2.0	16.5 (5)	Black	1 Pair x 26 AWG, 2 x 20 AWG	480Mbps
66-1123		1 & 3	USB-A (Male) to USB-miniB (Male) USB 2.0	6.5 (2)	Black	1 Pair x 26 AWG, 2 x 20 AWG	480Mbps
66-1128		1 & 3	USB-A (Male) to USB-miniB (Male) USB 2.0	16.5 (5)	Black	1 Pair x 26 AWG, 2 x 20 AWG	480Mbps

USB to Adapter Cables

Retail Part No.	Bulk Part No.	Figure No.(s)	Description	Length (Feet)	Color	Cable	Speed
45-1415		1 & 5	USB A (Male) to DB15 (Female)	6	Putty	1 Pair x 28 AWG, 2 x 24 AWG	12Mbps
45-1417		1 & 5	USB A (Male) to DB15 (Female)	12	Putty	1 Pair x 28 AWG, 2 x 24 AWG	12Mbps
45-1418		1 & 4	USB A (Male) to MD6 (Male)	6	Putty	1 Pair x 28 AWG, 2 x 24 AWG	12Mbps
45-1419		1 & 4	USB A (Male) to MD6 (Male)	12	Putty	1 Pair x 28 AWG, 2 x 24 AWG	12Mbps

IEEE-1284 Bi-directional Cables

Retail Part No.	Bulk Part No.	Figure No.(s)	Description	Length (Feet)	Color	Cable
45-1803		6 & 7	DB25 (Male)/CEN36 (Male)	3	Putty	18 Pairs x 28 AWG
45-1806		6 & 7	DB25 (Male)/CEN36 (Male)	6	Putty	18 Pairs x 28 AWG
45-1810		6 & 7	DB25 (Male)/CEN36 (Male)	10	Putty	18 Pairs x 28 AWG
45-1828		6 & 7	DB25 (Male)/CEN36 (Male)	25	Putty	18 Pairs x 28 AWG
45-1829		6 & 7	DB25 (Male)/CEN36 (Male)	50	Putty	18 Pairs x 28 AWG
45-1826		6 & 8	DB25 (Male)/half pitch CEN36 (Male)	6	Putty	18 Pairs x 28 AWG
45-1830		6 & 8	DB25 (Male)/half pitch CEN36 (Male)	10	Putty	18 Pairs x 28 AWG
45-2606		6 & 9	DB25 (Male)/DB25 (Female)	6	Putty	18 Pairs x 28 AWG
45-2610		6 & 9	DB25 (Male)/DB25 (Female)	10	Putty	18 Pairs x 28 AWG
45-2503		6	DB25 (Male)/DB25 (Male)	3	Putty	18 Pairs x 28 AWG
45-2506		6	DB25 (Male)/DB25 (Male)	6	Putty	18 Pairs x 28 AWG
45-2507		6	DB25 (Male)/DB25 (Male)	10	Putty	18 Pairs x 28 AWG
45-2525		6	DB25 (Male)/DB25 (Male)	25	Putty	18 Pairs x 28 AWG