



FK24M

Heavy duty T-handle long stem penetration probe



Copyright © 2007 Test Products International, Inc.

Application

General purpose penetration into
semi-solids and liquids

Range°F°C

-40° to 510°F
-40° to 265°C

Probe tip

21

Dimensions

Stem Length: 24" (610mm)
Diameter: Diameter: 0.37"/0.15"
(9.5mm/3.76mm)
Lead Length: 39.4" (1M)

Insulation Material

Polyurethane