



LED MOUNTS/SPACERS

T-1 (3mm) and T-1³/₄ (5mm) Individual LED Mounts



- 53 Different Sizes and Elevations
- Vertical Mounts Assure Accurate LED Positioning
- Compatible with 3mm or 5mm LEDs
- Molded from Natural Nylon per ASTM D-4066
- Made from 94V-2 Rated Nylon

Perfectly suited for in-line or grid alignment of LEDs, these T-1 (3mm) or T-1³/₄ (5mm) individual mounts provide a simple, effective solution to accurate LED placement, while standoffs on top and bottom allow for board cleaning and inspection.



460 Series

Color: Natural
Price Code: A

Part No.	H	T	F
460-060	.060 (1.5)	.040 (1.0)	.010 (.25)
460-070	.070 (1.8)	.040 (1.0)	.015 (.38)
460-080	.080 (2.0)	.040 (1.0)	.020 (.51)
460-090	.090 (2.3)	.040 (1.0)	.025 (.64)
460-100	.100 (2.5)	.040 (1.0)	.030 (.76)
460-110	.110 (2.8)	.040 (1.0)	.035 (.89)
460-120	.120 (3.0)	.040 (1.0)	.040 (1.0)
460-130	.130 (3.3)	.040 (1.0)	.045 (1.1)
460-140	.140 (3.6)	.040 (1.0)	.050 (1.3)
460-150	.150 (3.8)	.040 (1.0)	.055 (1.4)
460-160	.160 (4.1)	.040 (1.0)	.060 (1.5)
460-170	.170 (4.3)	.040 (1.0)	.065 (1.7)
460-180	.180 (4.6)	.040 (1.0)	.070 (1.8)
460-190	.190 (4.8)	.040 (1.0)	.075 (1.9)
460-200	.200 (5.1)	.040 (1.0)	.080 (2.0)
460-210	.210 (5.3)	.040 (1.0)	.085 (2.2)

461 Series

Color: Natural
Price Code: B

Part No.	H	T	F
461-360	.360 (9.1)	.340 (8.6)	.010 (.25)
461-380	.380 (9.7)	.340 (8.6)	.020 (.51)
461-400	.400 (10.2)	.340 (8.6)	.030 (.76)
461-420	.420 (10.7)	.340 (8.6)	.040 (1.0)
461-440	.440 (11.2)	.340 (8.6)	.050 (1.3)
461-460	.460 (11.7)	.340 (8.6)	.060 (1.5)
461-480	.480 (12.2)	.340 (8.6)	.070 (1.8)
461-500	.500 (12.7)	.340 (8.6)	.080 (2.0)
461-520	.520 (13.2)	.340 (8.6)	.090 (2.3)
461-540	.540 (13.7)	.340 (8.6)	.100 (2.5)

462 Series

Color: Natural
Price Code: F

Part No.	H	T	F
462-560	.560 (14.2)	.540 (13.7)	.010 (.25)
462-580	.580 (14.7)	.540 (13.7)	.020 (.51)
462-600	.600 (15.2)	.540 (13.7)	.030 (.76)
462-620	.620 (15.7)	.540 (13.7)	.040 (1.0)
462-640	.640 (16.3)	.540 (13.7)	.050 (1.3)
462-660	.660 (16.8)	.540 (13.7)	.060 (1.5)
462-680	.680 (17.3)	.540 (13.7)	.070 (1.8)
462-700	.700 (17.8)	.540 (13.7)	.080 (2.0)
462-720	.720 (18.3)	.540 (13.7)	.090 (2.3)
462-730	.730 (18.5)	.540 (13.7)	.095 (2.4)
462-740	.740 (18.8)	.540 (13.7)	.100 (2.5)

465 Series

Color: Natural
Price Code: B

Part No.	H	T	F
465-200	.200 (5.1)	.150 (3.8)	.025 (.64)
465-210	.210 (5.3)	.150 (3.8)	.030 (.76)
465-220	.220 (5.6)	.150 (3.8)	.035 (.89)
465-230	.230 (5.8)	.150 (3.8)	.040 (1.0)
465-240	.240 (6.1)	.150 (3.8)	.045 (1.1)
465-250	.250 (6.4)	.150 (3.8)	.050 (1.3)
465-260	.260 (6.6)	.150 (3.8)	.055 (1.4)
465-270	.270 (6.9)	.150 (3.8)	.060 (1.5)
465-280	.280 (7.1)	.150 (3.8)	.065 (1.7)
465-290	.290 (7.4)	.150 (3.8)	.070 (1.8)
465-300	.300 (7.6)	.150 (3.8)	.075 (1.9)
465-310	.310 (7.9)	.150 (3.8)	.080 (2.0)
465-320	.320 (8.1)	.150 (3.8)	.085 (2.2)
465-330	.330 (8.4)	.150 (3.8)	.090 (2.3)
465-340	.340 (8.6)	.150 (3.8)	.095 (2.4)
465-350	.350 (8.9)	.150 (3.8)	.100 (2.5)