



Search Results

- Evaluate
- FAQ's
- Design a Solution
- Part Drawings
- PDFSta-Strap Ca ..
- How to Buy
- Bill of Material
- Favorite Products List
- Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click to remove) Search Tips Within Results

Text Search: 'SST8H-L'

Your search criteria matched only one product, shown below

SST8H-L



- For indoor use
- Used for normal bundling and through -panel applications
- Small head height allows more efficient use of space in compact areas
- Exclusive two-piece design offers the lowest threading force in the industry
- Average 14% lighter than one -piece cable ties
- Releasable prior to final tensioning for bundle modifications
- Straight Tip design

Part Number	SST8H-L
RoHS Compliancy Status	Compliant
Part Description	Cable Tie, Releasable, 27.5", LightHeavy cross section
Product Type	Cable Ties
Material	Nylon 6.6
Color	Natural
CSA Certified	Yes
Mil. Std. Part Number	MS3367-6-9
UL Listed (File #E56854)	No
UL Recognized (File #E56854)	Yes
Length (In.)	27.5
Length (mm)	699
Width (In.)	.300
Width (mm)	7.6
CE Compliant	Yes
Cross Section	Light-Heavy
Head Height (In.)	.325
Head Height (mm)	8.3
Head Width (In.)	.460
Head Width (mm)	11.7
Locking Style	Releasable
Material Flammability Rating	UL 94V-2
Max. Bundle Diameter (In.)	8.00
Max. Bundle Diameter (mm)	203
Max. Continuous Use Temperature	185°F (85°C)
Min. Loop Tensile Strength (Lbs.)	120
Min. Loop Tensile Strength (N)	534
Pricing Description	Cable Tie, 2Piece, 27.5"L (699mm), LightHeavy, Nylon, Natural
Thickness (In.)	.067
Thickness (mm)	1.7
Tool	GTH, GS4H, GS4EH, PTH, STH2, ST3EH
Min. Order UOM	PC
Min. Order Qty.	50
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.