

| SIGN                                           | DATE | DESCRIPTION | APPROVER |
|------------------------------------------------|------|-------------|----------|
| △                                              |      |             |          |
| THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!! |      |             |          |

#### Materials

|                        |                                      |
|------------------------|--------------------------------------|
| Item 1 insulating body | Thermoplastic (UL94V-0)              |
| Item 2 Steel screw     | Screw, Zinc plating("+/-" slot type) |
| Item 3 Wire guard      | Stainless steel                      |
| Item 4 Terminal body   | Brass Tin plated                     |

#### Electrical

- Voltage rating: 300VAC
- Current rating: 8A
- Wire range:
  - Solid wire(AWG): 14-26
  - Stranded wire(AWG): 14-26
- Torque(Lb-In): 2.6
- Screw: M2.5
- Wire strip length: 5-6mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -30°C to +105°C
- Soldering temperature: 250°C±10°C/5 Sec

RoHS Compliant

PART NUMBER:

**OSTT3XX0453**


No. of Poles  
 02: 2 Poles  
 03: 3 Poles  
 ...  
 24: 24 Poles

COLOR  
 0: Black  
 5: Green (Standard)  
 6: Blue  
 8: Grey


THESE DRAWINGS AND SPECIFICATIONS  
 ARE THE PROPERTY OF ON-SHORE  
 TECHNOLOGY, INC. AND SHALL NOT BE  
 REPRODUCED, COPIED OR USED IN ANY  
 MANNER WITHOUT THE PRIOR WRITTEN  
 CONSENT OF ON-SHORE TECHNOLOGY,  
 INC.

**OST** ON-SHORE TECHNOLOGY, INC.

|          |                      |          |          |              |                 |             |            |
|----------|----------------------|----------|----------|--------------|-----------------|-------------|------------|
| TITLE    | OSTT3 5.0 Series 90° |          |          |              |                 |             |            |
| PART NO. | OSTT3XX0453          |          |          | DWG NO.      | OSTT3XX0453.DWG |             |            |
| APPROVED | CHECKED              | DESIGNED | DRAWN    | CUST NO.     |                 |             |            |
|          |                      | 熊海燾      | 熊海燾      |              |                 |             |            |
|          |                      | 11/08/06 | 11/08/06 |              |                 |             |            |
|          |                      |          |          | SHEET: 01/01 |                 | UNIT: mm    | Tolerance  |
|          |                      |          |          |              |                 | SCALE: NONE | X. ±0.50   |
|          |                      |          |          |              |                 | REV: B      | X.X ±0.30  |
|          |                      |          |          |              |                 |             | X.XX ±0.10 |
|          |                      |          |          |              |                 |             | X° ±1°     |



N=Number of poles



P.C.B. LAYOUT