




1.57	.062	-	-
1.52	.060	16.89	.665
1.50	.059	5.08	.200
1.40	.055	2.67	.105
1.37	.054	2.41	.095
0.76	.030	2.29	.090
0.20	.008	2.16	.085
0.13	.005	2.08	.082
0.00127	.000050	1.93	.076
0.00076	.000030	1.91	.075
MM	IN	MM	IN
CONVERSION TABLE			

3	0.20 BRASS	1.52 MAX	0.5 - 0.2 mm ² (30-24 AWG)	640391-5	
PRE-TIN	0.20 BRASS	1.52 MAX	0.5 - 0.2 mm ² (30-24 AWG)	640391-1	
FINISH	MATERIAL	INSULATION DIAMETER	WIRE RANGE	PART NO	
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm TOLERANCES ON : 2 PLC DEC ± .1 3 PLC DEC ± 0.13 ANGLES ± -		DR 9-12-90 B. LEWIS CHK 9-13-90 R. SWING APPD 9-27-90 C. CASH APPD 9-27-90 C. CASH PRODUCT SPEC -	AMP AMP Incorporated Harrisburg, PA 17105-3608 NAME .062 PIN, COMMERCIAL PIN AND SOCKET		
MATERIAL	SEE TABLE		SIZE	CAGE CODE	DRAWING NO
FINISH	SEE TABLE	APPLICATION SPEC - WEIGHT _	D	00779	640391
			SCALE	8:1	SHEET 1 OF 1

METRIC