

Search Results

Evaluate

- Brochures
- PDF-Space Saving ..
- FAQ's

Design a Solution

- Catalog Cut Sheet
- PDF-R4P23 Produc
- Part Drawings
- DWG-4 POST Rack ..
- PDF-4 POST Rack ..
- DXF-4 POST Rack ..
- Specification Sheets
- PDF-2 Post and 4 ..
- PDF-NetManager H ..
- PDF-4 Post Rack ..

How to Buy

- Bill of Material
- Favorite Products List
- Locate Distributor

Install & Maintain

- Installation Instructions
- PDF-4 Post Rack ..

Home > Product On-Line Catalog > Search Results >

Current refinements (click ☐ to remove) Search Tips [?](#)

☒ Text Search: 'R4P42'

Your search criteria matched only one product, shown below

R4P42



- Independent adjustable front and rear mounting rails can be adjusted while the rack is secured to the floor
- Printed rack space identification on all equipment rails allows for quick location of rack spaces, speeding installation of rack mount items (Shipped numbers up per TIA606 specifications. Can be set to number down by flipping the rails.)
- Rack is UL listed for 2,500 lbs. load rating
- Rear rail construction provides a clear ventilation path for side ventilated switches
- Multiple mounting holes in top flanges for securing ladder rack
- Weld nut construction eliminates the need for a second wrench increasing speed and ease of assembly
- Multiple mounting locations for vertical power strips on any of the four posts or on the adjustable mounting rails
- PatchRunner™ and NetRunner™ Vertical Cable Managers mount directly to the 4 Post Rack at any of the four corners to provide a flexible end-to-end cable management solution

▪ Paint piercing washers included to electrically bond rack for simplified grounding. For the complete grounding solution, see the StructuredGround™ Kits

▪ Part Number	R4P42
▪ RoHS Compliancy Status	Compliant
▪ Part Description	4 post EIA rack with #12-24 threaded rails. Dimensions: 84.0"H x 23.25"W x 41.5"D (2134mm x 591mm x 1054mm).
▪ Product Type	Rack
▪ Color	Black
▪ Depth (In.)	41.5
▪ Depth (mm)	1054
▪ Diameter (In.)	41.7
▪ Diameter (mm)	1059
▪ Height (In.)	84.0
▪ Height (mm)	2134
▪ Width (In.)	23.25
▪ Width (mm)	591
▪ No. of Rack Spaces	45
▪ Pricing Description	42" Deep 4 Post Rack
▪ Min. Order UOM	PC
▪ Min. Order Qty.	1
▪ BOM Qty. (# of Pkgs.)	0
▪ Add to Favorite Product List	☐

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.