


REV.	DATE	ECR NO.	DESCRIPTION
NC	10/16/09	XXXXXX	INITIAL RELEASE



CENTER CONTACT TO ACCEPT $\phi .022$ TO $\phi .042$ PIN [$\phi 0.56$ TO $\phi 1.07$]

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020"					APPROVALS		DATE		Amphenol Connex						
					DRAWN		M.ZHANG							10/16/09	
					CHECKED										
					ISSUED						PART DESCRIPTION F PANEL JACK				
					SHEET		1 OF 1								
											PART NO. 222146				
						DWG. NO. 222146.DWG					REV. NC	SIZE A	SCALE NA		
						CAD FILE C:/CONNEX/222146.DWG									
DO NOT SCALE DRAWING															

6	LOCK RING	BRASS	NICKEL	1
5	GASKET	SILICONE	RED	1
4	INSULATOR	PTFE	NATURAL	1
3	CONTACT PIN	BRASS	BRIGHT TIN	1
2	INSULATOR	PTFE	NATURAL	1
1	BODY	BRASS	NICKEL	1
	DESCRIPTION	MATERIAL	FINISH	QTY