

Data sheet

Free-standing Portable G ½ Filter-Regulator-Lubricator Cradle, with Gauge and Carry Handle.



Technical Data

- Maximum Operating Temperature: +50°C
- Minimum Operating Temperature: -10°C
- Pressure Range: 0 to 8 bar
- Maximum Inlet Pressure: 15 bar
- Maximum Flow: 2500 lpm

RS Stock Number : 784-0085
G ½ FRL Portable Air Cradle
20 micron filtration standard

