

REDINGTON COUNTERS, INC.
P.O. Box 608, 130 Addison Road, Windsor, CT 06095
Toll Free: (860) 688-6205 • Fax: 860/688-1591
E-Mail: Info@RedingtonCounters.com • Website: www.RedingtonCounters.com

Item # 3-2835, Model 28 Mechanical Stroke Counter



Model 28 Mechanical Stroke Counter

A 5 figure, rugged stroke counter, with right-hand shaft extension, operating lever and attached spring. Rated at 600 counts per minute, this heavy-duty model is well suited for most industrial applications.

SPECIFICATIONS

Model No.	28
Display	5 Figures, white on black, 0.27 inch (7mm) high
Display Height	0.27 Inch
Display Height	7 mm
No. of Digits	5
Speed	600 counts/minute
Operating Temperature	-15 to +140 °F
Operating Temperature	-26 to +60 °C
Reset Type	Internal
Mounting Hole Dia.	0.18 Inch
Mounting Hole Dia.	4.6 mm
Weight	20 oz
Weight	567 gm
Operating Life	Beyond 200 million counts
Rotation	Top-coming
Shaft Extension	Right-hand
Minimum Count Stroke	36 °
Maximum Count Stroke	45 °
Stock Availability	No