

HC-B 24-AMQ-EMV

Order No.: 1642962

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1642962>

HEAVYCON panel mounting base B24, with double locking latch,
EMC version. Not suitable for D series terminal adapters

Commercial data

GTIN (EAN)	 4 046356 028608
sales group	D002
Pack	10 pcs.
Customs tariff	85389099
Catalog page information	Page 519 (PC-2009)

Product notes

WEEE/RoHS-compliant since:
07/03/2006



[http://
www.download.phoenixcontact.com](http://www.download.phoenixcontact.com)
Please note that the data given
here has been taken from the
online catalog. For comprehensive
information and data, please refer
to the user documentation. The
General Terms and Conditions of
Use apply to Internet downloads.

Technical data


General data

Note	For contact inserts HC-B24, BB46, D64, DD108, M
Design	B24
Height	30.5 mm
Width	48 mm

Length	140 mm
Housing type	EMC housings
Locking type	With double locking latch
Degree of protection	IP65
Ambient temperature (operation)	-40 °C ... 100 °C
Housing material	Aluminum, die-cast
Housing surface material	EMC coating, silver
Seal material	NBR, conductive
Material lock	Steel, galvanized
Length of the assembly cutout	108 mm
Width of the assembly cutout	35 mm
Assembly instructions	Cannot be used for HC-D... series terminal adapters.
Connection	If insulating powder coating is present on the control cabinet panel, it should be removed from the profile gasket area in order to ensure optimum shielding.


Diagrams/Drawings

Diagram





Shield attenuation

Dimensioned drawing



Dimensional drawing



Panel cutout

Address

PHOENIX CONTACT Deutschland GmbH
Flachsmarktstr. 8
32825 Blomberg, Germany
Phone +49 5235 3 12000
Fax +49 5235 3 41200
<http://www.phoenixcontact.de>



© 2010 Phoenix Contact
Technical modifications reserved;