

FireWire IEEE 1394 Cable (4pin/4pin M/M) 6-ft.

MODEL NUMBER: **F009-006**



Description

Tripp Lite's 6 ft. IEEE 1394 Firewire 4-pin to 4-pin cable supports data transfer rates up to 400Mbps, and features both gold-plated contacts and connectors for superior conductivity. Premium double-shielded cable with both a braid and a foil shield to virtually eliminate crosstalk and reduce EMI/RFI interference.

Features

- Premium quadruple-shielded cables with tinned copper braid and aluminum mylar foil on each twisted pair as well as on the cable as a whole.
- Supports data transfer rates up to 400Mbps.
- Gold plated connectors provide superior conductivity.

Specifications

INPUT	
Cable Length (ft.)	6
Cable Length (m)	1.8
PHYSICAL	
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.17
Shipping Weight (kg)	0.08
Color	Black

Highlights

- Premium quadruple-shielded cables with tinned copper braid and aluminum mylar foil on each twisted pair as well as on the cable as a whole
- Supports data transfer rates up to 400Mbps
- Gold plated connectors provide superior conductivity

Package Includes

- 6 ft. IEEE 1394 Firewire 4-pin to 4-pin. cable with Gold connectors

CONNECTIONS	
Side A - Connector 1	4 PIN (MALE)
Side B - Connector 1	4 PIN (MALE)
CERTIFICATIONS	
Certifications	RoHS-Compliant
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2018 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>