

SHF-110-01-L-D-RA

ESHF-125-01-L-D-SM-LC

EHF-108-01-F-D-SM-LC

ESHF-105-01-L-D-SM

EHF-125-01-L-D-SM-LC

SHF, ESHF, EHF, ECF SERIES

(1,27 mm) .050"

SHROUDED & EJECTOR IDC HEADER

SHF, ESHF Mates with:

FFSD, FFTP (SHF)

EHF Mates with:

FFSD*, FFTP

SPECIFICATIONS

For complete specifications see www.samtec.com?SHF, www.samtec.com?ESHF or www.samtec.com?EHF

Insulator Material:
Black Liquid Crystal Polymer

Terminal Material:
Phosphor Bronze

Plating:
Sn or Au over

50µ" (1,27 µm) Ni

Operating Temp Range:
-55°C to +125°C

RoHS Compliant:
Yes

Processing:
Lead-Free Solderable:

Yes

SMT Lead Coplanarity:
(0,10 mm) .004" max

RECOGNITIONS


For complete scope of recognitions see www.samtec.com/quality



ALSO AVAILABLE (MOQ Required)

- Other sizes
- Contact Samtec.

EJECTOR HEADER CAP (Locks FFSD cable to EHF header)





ECF

NO. PINS PER ROW

05, 08, 10,
13, 17, 20, 25

***Important Note:**
EHF will not mate to FFSD with strain relief (-SR option), see ESHF series.

Note: Some lengths, styles and options are non-standard, non-returnable.


WWW.SAMTEC.COM

Due to technical progress, all designs, specifications and components are subject to change without notice.