

[Industrial Products](#) > [Connectors](#) > [Non-Sealed and Audio Connectors](#) > [DIN](#) > [DIN Cable Mount](#)



DIN Cable Mount

Male and female cord plug with shielded barrel or insulated snaplock plastic body. Two piece metal barrel surrounds pin insert to form an electrical shield. The entire insert assembly is held together by snapping the insulated plastic shell over the assembly. The barrel's special metal tab locks the shell in place. Standard color of plastic shell is gray. All-purpose cable clamp.

[enlarge](#)

Products	Specifications	Need more info? Contact Switchcraft customer service
----------	----------------	--

Product	Description	Typical Mating	Layout	Drawings	Distributor Inventory	
03BL2M	DIN Cable Mount Connector, male cord plug with ground key-rib, 2 pins with insulated switch actuator		Pin Arrangements 1		check stock	
05BL3MX	DIN Cable Mount Connector, male cord plug with ground key-rib, 3 pins at 180°		Pin Arrangements 2		check stock	
05BL5MX	DIN Cable Mount Connector, male cord plug with ground key-rib, 5 pins at 180°		Pin Arrangements 5		check stock	
05DL5MX	DIN Cable Mount Connector, right angle male plug, black strain relief, 5 pins at 180°		Pin Arrangements 5		check stock	
05GM3MX	DIN Cable Mount Connector, male cord plug with shielded barrel, 3 pins at 180°, gray body and strain relief		Pin Arrangements 2		check stock	
05GM5MX	DIN Cable Mount Connector, male cord plug with shielded barrel, 5 pins at 180°, Gray body and strain relief		Pin Arrangements 5		check stock	
06AL5FX	DIN Cable Mount Connector, female receptacle with ground contact, 5 contacts at 180°		Contact Arrangements F		check stock	
09BL4MX	DIN Cable Mount Connector, male cord plug with ground key-rib,4 pins at 210°		Pin Arrangements 3		check stock	
09GM4MX	DIN Cable Mount Connector, male cord plug with shielded barrel, 4 pins at 210°, Gray body and strain relief		Pin Arrangements 3		check stock	
12BL5MX	DIN Cable Mount Connector, male cord plug with ground key-rib, 5 pins at 240°		Pin Arrangements 4		check stock	
12BL6MX	DIN Cable Mount Connector, male cord plug with ground key-rib, 6 pins at 240°		Pin Arrangements 6		check stock	
12DL5M	DIN Cable Mount Connector, right angle male plug, black strain relief, 5 pins at 240°		Pin Arrangements 4		check stock	
12DL6M	DIN Cable Mount Connector, right angle male plug, black strain relief, 6 pins at 240°		Pin Arrangements 6		check stock	
12GM5MX	DIN Cable Mount Connector, male cord plug with shielded barrel, 5 pins at 240°, Gray body and strain relief		Pin Arrangements 4		check stock	
12GM6MX	DIN Cable Mount Connector, male cord plug with shielded barrel, 6 pins at 240°, Gray body and strain relief		Pin Arrangements 6		check stock	
13AL5F	DIN Cable Mount Connector, female receptacle with ground contact, 5 contacts at 240°		Contact Arrangements E		check stock	
13AL6F	DIN Cable Mount Connector, female receptacle with ground contact, 5 contacts at 240°		Contact Arrangements G		check stock	
15AL7F	DIN Cable Mount Connector, female receptacle with ground contact,7 contacts at 270°		Contact Arrangements H		check stock	
15AL8FX	DIN Cable Mount Connector, female receptacle with ground contact, 8 contacts at 270°		Contact Arrangements N		check stock	
15BL7M	DIN Cable Mount Connector, male cord plug with ground key-rib, 7 pins at 270°		Pin Arrangements 7		check stock	
15BL8MX	DIN Cable Mount Connector, male cord plug with ground key-rib, 7 pins at 270°		Pin Arrangements 8		check stock	
15GM7MX	DIN Cable Mount Connector, male cord plug with shielded barrel, 7 pins at 270°, Gray body and strain relief		Pin Arrangements 7		check stock	
15GM8MX	DIN Cable Mount Connector, male cord plug with shielded barrel, 8 pins at 270°, Gray body and strain relief		Pin Arrangements 9		check stock	
20BL8M	DIN Connector Receptacle				check stock	
20GM8MX	DIN Cable Mount Connector, male cord plug with shielded barrel, 8 pins at 262°, Gray body and strain relief		Pin Arrangements 10		check stock	

denotes a special order