

**JACKPAC
JP TEST****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The following products are available as functional components:

- Switch and button components in a sealed built-in EG2 enclosure
- Rectifier and fuse components in a sealed built-in EG2 enclosure
- Logic components with AND, NAND, OR and NOR operators
- Diode gates with up to 40 inputs in open design
- Components modules for the integration of electronic elements
- Serial interface converter, and AD / DA converter

General ordering data

Order No.	8794120000
Type	JP TEST
Version	JACKPAC, Relays, Rated control voltage: 18...24...30 V DC, Continuous current: 2 A, M12 plug/socket, A-coded
GTIN (EAN)	4032248483969
Qty.	1 pc(s).

**JACKPAC
JP TEST**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Length	83 mm	Width	36 mm
Height	14.4 mm	Net weight	36 g

Temperatures

Operating temperature	0 °C...+55 °C	Ambient temperature	0 °C...+55 °C
Storage temperature	-25 °C...+70 °C		

Input

Rated control voltage	18...24...30 V DC	Rated current DC	2.2 mA (LED)
Status indicator	Green LED		

Output

Continuous current	2 A	Power	2.2 mA at 24 V
--------------------	-----	-------	----------------

Rated data

Conductor connection system	M12 plug/socket, A-coded
-----------------------------	--------------------------

Insulation coordination (EN 50 178)

Protection degree	IP 67
-------------------	-------

Classifications

ETIM 3.0	EC001134	UNSPSC	30-21-18-01
eClass 6.0	27-20-11-90	eClass 7.0	27-20-11-90

Approvals

Approvals

