

Specifications:
 Current Rating:1.0A AC/DC
 Voltage Rating:30V AC/DC
 Contact Resistance:20m ohm. Max.
 Insulation Resistance:1000M ohm. Min.
 Withstanding Voltage:500V AC For One Minute
 Operating Temperature Rating:-40°C ~ + 105°C
 Materials and Finish
 Insulator:PBT (UL94V-0)
 Insulator Color:Black
 Contact:Copper Alloy
 Plated:Selective Gold Plated


TOTAL NO. OF PINS	DIM		
	A±0.30	B±0.15	C±0.30
10	32.00	10.16	17.40
14	37.08	15.24	22.48
16	39.62	17.78	25.02
20	44.70	22.86	30.10
24	49.78	27.94	35.18
26	52.32	30.48	37.72
30	57.40	35.56	42.80
34	62.48	40.64	47.88
40	70.10	48.26	55.50
50	82.80	60.96	68.20
60	95.50	73.66	80.90
64	100.58	78.74	85.98

RoHS Compliant


				DRAWN:	GENERAL TOLERANCE: .X=±0.20 .XX=±0.15	CnC Tech Industrial Cable and Connector Technology	
E							
D				CHECKED:	UNIT: MM	DESCRIPTION: 2.54mm IDC Ejector Header Type	SIZE A4
C	13-Dec-2013				SCALE:1:1		
B	19-Feb-2013			APPROVAL:	SHEET: 1 / 2	PART NO: 3010-XX-041-11-00	
A	14-Feb-2006				PROJECTION: 		
REV	DATE	FILE	BY				

Note:
1.Dimension:
Tray Size:450(L)x260(W)x19(H) (MM)
Carton Size:470(L)x280(W)x200(H) (MM)
2.Quantity
10 Tray/Carton

Circuits	PCS/Tray	Q'ty/Carton
10	156	1560
14	132	1320
16	120	1200
20	108	1080
24	96	960
26	96	960
30	84	840
34	72	720
40	72	720
50	60	600
60	48	480
64	48	480



RoHS Compliant

				DRAWN:	GENERAL TOLERANCE: .X=±0.20 .XX=±0.15	CnC Tech Industrial Cable and Connector Technology		D
E								
D				CHECKED:	UNIT: MM	DESCRIPTION: 2.54mm IDC Ejector Header Type	SIZE A4	
C	13-Dec-2013				SCALE:1:1			
B	19-Feb-2013			APPROVAL:	SHEET: 2 / 2	PART NO: 3010-XX-041-11-00		
A	14-Feb-2006				PROJECTION: 			
REV	DATE	FILE	BY					