





Dimensions: mm (In.)



Mechanical Specifications:

- Mechanical life: 10,000 operation min. per switch
- Operation force: less than 800g

Electrical Specifications:

- Electrical life: 5,000 operation min. per switch
- Rating: Non-switching 100mA/50VDC;
Switching 50mA/24VDC

Note:

- RoHS Compliant and Process Compatible with 260° solder

Mouser Stock No.	No. of Positions	Dimension "A" (In.)	Type
106-1254-EV	4	.439	SPST
106-1258-EV	8	.839	SPST

Right Angle DIP Switches
106-1254-EV, 106-1258-EV



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[106-1258-EV](#) [106-1254-EV](#)