



Liquidtight Flexible Metal Conduit Fittings T&B Catalog Number:

5333-HT

78621090949

Status:

Active

Description:

3/4 in. straight steel insulated liquidtight high temperature connector.

Features

Sure-Tight gland deflects water away from connector and prevents "pooling" of moisture.

Double beveled sealing ring designed with 5 unique sealing mechanisms and cannot be installed backwards

Safe Edge ground cone provides superior bonding, stronger pullout, easy threading and conductor protection.

Double plating for superior corrosion protection

Heat Curled Insulator molded inside body provides excellent wire protection and easier glide of conductors through and into the fitting.

General

Style	Insulated
-------	-----------

Trade Size (inches)	3/4
---------------------	-----

Material	Steel
----------	-------

Finish	Zinc Plating/Clear Chromate
--------	-----------------------------

Dimension Information

Dimension A (inches)	1 21/32
----------------------	---------

Dimension B (inches)	1 5/8
----------------------	-------

Dimension C (inches)	9/16
----------------------	------

Specifications

3dmodel	Available on Website
---------	----------------------

Packaging

T&B Inner Pack	25
----------------	----

Package in Units	50
------------------	----

T&B Sold in UOM	Each
-----------------	------

T&B Weight Per UOM	22.5 lbs. per 100
--------------------	-------------------

Application Support

304 Stainless Steel Corrosion Compatibility Chart Available on Website

T&B Sales Drawings

wsd-000016

T&B Instruction Sheets

ta02544-tb2

Product Brochure

Available on Website

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:

E 23018

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com