


## CPC Accessories

### Peripheral Seals (For Receptacles Only)



Suggested for sealing connectors to protect from vibration and moisture. Grey elastomer.

| Stock No. | Mfr.'s Type | Shell Size | Dim. A |       | Dim. B |      | EACH |         |         |
|-----------|-------------|------------|--------|-------|--------|------|------|---------|---------|
|           |             |            | In.    | mm    | In.    | mm   | 1-99 | 100-499 | 500-999 |
| 512-1290  | 206403-1    | 11         | 0.524  | 13.31 | 0.041  | 1.04 | .51  | .46     | .38     |
| 512-1292  | 206403-4    | 13         | 0.650  | 16.51 | 0.041  | 1.04 | .75  | .67     | .56     |
| 512-1294  | 206403-2    | 17         | 0.875  | 22.23 | 0.050  | 1.27 | .58  | .52     | .43     |
| 512-1296  | 206403-3    | 23         | 1.230  | 31.24 | 0.050  | 1.27 | 1.04 | .94     | .78     |

### Sealing Caps (For Receptacles Only)

Used to protect exposed contacts on unmated receptacles. Black thermoplastic cap with plastic strap or beaded chain.

| Stock No. | Mfr.'s Type | Shell Size | Dimensions — In. (mm) |               | EACH |       |         |
|-----------|-------------|------------|-----------------------|---------------|------|-------|---------|
|           |             |            | A                     | B             | 1-49 | 50-99 | 100-499 |
| 512-1240  | 206903-1    | 11         | 0.360 (9.14)          | 0.927 (23.55) |      |       |         |
| 512-1241  | 211870-1    | 13         | 0.360 (9.14)          | 1.055 (26.80) |      |       |         |
| 512-1242  | 207445-1    | 17         | 0.360 (9.14)          | 1.295 (32.89) |      |       |         |
| 512-1243  | 207446-1    | 23         | 0.460 (11.68)         | 1.728 (43.89) |      |       |         |

### With Plastic Strap



| Stock No. | Mfr.'s Type | For Series | Size | EACH |       |         |
|-----------|-------------|------------|------|------|-------|---------|
|           |             |            |      | 1-24 | 25-99 | 100-499 |
| 512-1240  | 206903-1    | 1 and 2    | 11   | 2.86 | 2.57  | 2.14    |
| 512-1241  | 211870-1    | 1          | 13   | 2.61 | 2.35  | 1.96    |
| 512-1242  | 207445-1    | 1, 2 and 3 | 17   | 3.08 | 2.77  | 2.31    |
| 512-1243  | 207446-1    | 1, 3 and 4 | 23   | 3.56 | 3.20  | 2.67    |

### With Beaded Chain

| Stock No. | Mfr.'s Type | For Series | Size | 1-24 | 25-99 | 100-499 |
|-----------|-------------|------------|------|------|-------|---------|
| 512-1245  | 208800-1    | 1 and 2    | 11   | 4.78 | 4.30  | 3.59    |
| 512-1246  | 208652-1    | 1, 2 and 3 | 17   | 4.60 | 4.14  | 3.45    |
| 512-1247  | 208680-1    | 1, 3 and 4 | 23   | 5.53 | 4.98  | 4.15    |

## Metal-Shell CPC Connectors

The four series of Metal shell CPC connectors require the same contacts and tools as like series of Circular plastic connectors. **Contacts are sold separately**. Because of the larger size, a different series of cable clamps are offered. **Material Insert:** Black thermoplastic. **Shells and Coupling Ring:** Aluminum alloy, zinc-plated. **Retainer Ring:** Stainless steel.



### Series 2

These connectors use AMPLIMITE® type 20DF and 20DM contacts and tools that are listed with AMPLIMITE® D-Sub connectors in this catalog.

### Standard Sex Plugs without Tetraseal (For Socket Contacts)

| Stock No. | Mfr.'s Type | Size | No. of Contacts | EACH  |       |       |
|-----------|-------------|------|-----------------|-------|-------|-------|
|           |             |      |                 | 1-24  | 25-49 | 50-99 |
| 512-1158  | 208718-1    | 14   | 5               | 42.09 | 38.26 | 35.07 |
| 512-1159  | 208714-1    | 14   | 7               | 29.21 | 26.56 | 24.34 |
| 512-1161  | 208488-1    | 22   | 16              | 27.23 | 24.76 | 22.70 |
| 512-1162  | 208457-1    | 28   | 24              | 34.78 | 31.62 | 28.99 |
| 512-1163  | 208470-1    | 28   | 37              | 34.78 | 31.62 | 28.99 |

### Standard Sex Square Flange Receptacles (For Pin Contacts)

|          |          |    |    |       |       |       |
|----------|----------|----|----|-------|-------|-------|
| 512-1164 | 208719-1 | 14 | 5  | 17.54 | 15.95 | 14.64 |
| 512-1165 | 208715-1 | 14 | 7  | 18.30 | 16.64 | 15.25 |
| 512-1168 | 208489-1 | 22 | 16 | 24.05 | 21.87 | 20.04 |
| 512-1169 | 208459-1 | 28 | 24 | 27.54 | 25.04 | 22.95 |

### Reverse Sex Plugs without Tetraseal (For Pin Contacts)

|          |          |    |    |       |       |       |
|----------|----------|----|----|-------|-------|-------|
| 512-1177 | 208720-1 | 14 | 5  | 31.23 | 28.39 | 26.03 |
| 512-1179 | 208716-1 | 14 | 7  | 28.56 | 25.96 | 23.80 |
| 512-1181 | 208486-1 | 22 | 14 | 28.29 | 25.72 | 23.58 |
| 512-1183 | 208472-1 | 28 | 37 | 33.33 | 30.30 | 27.78 |

### Reverse Sex Square Flange Receptacles (For Pin Contacts)

|          |          |    |    |       |       |       |
|----------|----------|----|----|-------|-------|-------|
| 512-1185 | 208721-1 | 14 | 5  | 19.97 | 18.16 | 16.64 |
| 512-1187 | 208717-1 | 14 | 7  | 18.30 | 16.64 | 15.25 |
| 512-1189 | 208487-1 | 22 | 14 | 21.54 | 19.58 | 17.95 |
| 512-1191 | 208473-1 | 28 | 37 | 27.52 | 25.02 | 22.93 |

### Standard Sex Plugs without Tetraseal (For Pin Contacts)

|          |          |    |    |       |       |       |
|----------|----------|----|----|-------|-------|-------|
| 512-1192 | 208722-1 | 14 | 5  | 19.97 | 18.16 | 16.64 |
| 512-1194 | 208724-1 | 14 | 7  | 18.30 | 16.64 | 15.25 |
| 512-1196 | 208488-1 | 22 | 14 | 21.54 | 19.58 | 17.95 |
| 512-1198 | 208474-1 | 28 | 37 | 27.52 | 25.02 | 22.93 |

### Standard Sex Plugs without Tetraseal (For Pin Contacts)

|          |          |    |    |       |           |       |
|----------|----------|----|----|-------|-----------|-------|
| 512-1199 | 208725-1 | 14 | 5  | 19.97 | 18.16     | 16.64 |
| 512-1200 | 208726-1 | 14 | 7  | 18.30 | 16.64     | 15.25 |
| 512-1202 | 208489-1 | 22 | 14 | 21.54 | 19.58</td |       |