



Wire Joints

T&B Catalog Number:

54610

UPC Number:

78621054610

Status:

Active

Description:

Copper Cable Joint for Wire Range Min: 3 #12 Sol. or Str., Max: 2 #10 w/1 #12 Sol. or Str., Blue Die

Features

Ideal for pigtail, tapping multiple conductors or 2-way splicing. Offers lowest installed cost.

Form a permanent installation in minimal space.

Easily insulated.

Color-coded to dies for positive matching and compression.

General

Material	Copper
Finish	Tin-Plated
Die Color	Blue
Die Code	24
Connector Range Min.	3 #12 Sol. or Str.
Connector Range Max.	2 #10 w/1 #12 Sol. or Str.
Circular Mil Area Min.	19590
Circular Mil Area Max.	27290

Dimension Information

A (inches)	.407
E (inches)	.37

Specifications

Voltage Rating	600V
----------------	------

Tooling

Application Tools	TBM25S, TBM8, TBM8S, TBM5, TBM5S, TBM6, TBM6S
TBM8/8S Die Catalog Number	13461
TBM5/5S Die Catalog Number	13454
TBM6/6S Die Catalog Number	13475, 13477
Connector & Tooling Chart	Available on Website

Packaging

T&B Order Multiple	20
T&B Inner Pack	20
Package in Units	200
T&B Sold in UOM	Each
T&B Weight Per UOM	0.5 lbs. per 100

Application Support

Popular Wire Combinations	Available on Website
---------------------------	----------------------

Notes

Hand tools only.

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:
E9809

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com