

607 Series 7 mm Panel Mount Indicators



Dimensions

inches [mm]




Figure 1




Figure 2




Figure 3




Figure 4

Certifications & Ratings

- RoHS compliant
- NEMA 4X (Watertight only)
- IP66 (Watertight only)

Application

The 607 Series LED Panel Mount Indicators are designed for a variety of applications such as:

- Main power indication
- Remote power indication
- Status indication
- Maintenance and warning indication
- Instrumentation

... and many more!

Mechanical Information

Mounting Hole Size: 0.283" (7.2 mm)

Max Panel Thickness: See part numbers

Mounting Torque: 0.362 lbs/ft (5 kg/cm)
0.217 lbs/ft or 3 kg/cm (Figure 5 only)

Specifications

Voltage Options: 2 VDC (resistor required)
6, 12 & 24 VDC (no resistor required)

Operating Temp: -30°C to +85°C (-22°F to +185°F)

Storage Temp: -40°C to +85°C (-40°F to +185°F)

Electrical Connection: Solder terminals

Housing: Protruding & recessed positions:
Brass—Chrome Plated
Internal position: Polycarbonate

Terminals: Copper—Nickel Plated

Lock Washer: Iron—Nickel Plated

Nut: Brass—Nickel Plated




Figure 5

Ordering Information 607 Series

Standard		Watertight						
Part Number	Part Number	Color	Voltage (VDC)	Current (mA)	Intensity Typ. (mcd)	LED Positions	Figure	Panel Thickness
607-1112-110F	607-1112-310F	Red	2	15	40	Protruding	1	0.187" (4.75 mm)
607-1212-110F	607-1212-310F	Green			65			
607-1312-110F	607-1312-310F	Yellow			55			
607-1112-120F	607-1112-320F	Red	6		40		2	0.265" (6.75 mm)
607-1212-120F	607-1212-320F	Green			65			
607-1312-120F	607-1312-320F	Yellow			55			
607-1112-130F	607-1112-330F	Red	12		40			
607-1212-130F	607-1212-330F	Green			65			
607-1312-130F	607-1312-330F	Yellow			55			
607-2112-110F	607-2112-310F	Red	2		65	Recessed	3	0.136" (3.45 mm)
607-2212-110F	607-2212-310F	Green			85			
607-2312-110F	607-2312-310F	Yellow			70			
607-2112-120F	607-2112-320F	Red	6		65		4	0.336" (8.50 mm)
607-2212-120F	607-2212-320F	Green			85			
607-2312-120F	607-2312-320F	Yellow			70			
607-2112-130F	607-2112-330F	Red	12		65			
607-2212-130F	607-2212-330F	Green			85			
607-2312-130F	607-2312-330F	Yellow			70			
607-3132-120F	607-3132-320F	Red	6		35	Internal	5	0.187" (4.75 mm)
607-3232-120F	607-3232-320F	Green			45			
607-3332-120F	607-3332-320F	Yellow			40			
607-3132-130F	607-3132-330F	Red	12		35			
607-3232-130F	607-3232-330F	Green			45			
607-3332-130F	607-3332-330F	Yellow			40			
607-3132-140F	607-3132-340F	Red	24		35			
607-3232-140F	607-3232-340F	Green			45			
607-3332-140F	607-3332-340F	Yellow			40			