


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION MAY , 2005.

© COPYRIGHT 2005 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC		DIST		REVISIONS			
J				変更			
P	LTR	DESCRIPTION		DATE	DWN	APVD	
	B	REVISED ECR-06-006457		16MAR06	J.T	T.K	



注記

1.材料 ハウジング、スライダ：熱可塑性樹脂 UL 94-V 色：黒
コンタクト：銅合金
シェル：銅合金
コイル：SWP
カムロッド：SUS
フックスプリング：SUS

2 仕上げ コンタクト：Ni下地めっき
接点部：金めっき
シェル：Ni下地めっき
金めっき


△ 非累積公差
4. コプラナリティは 0.1mm以下
△ スイッチ可動エリア
△ ボス無しタイプには適用なし
△ スイッチ回路図


注記


1.MATERIAL HOUSING,SLIDER : THERMOPLASTIC RESIN
UL94V-0, COLOR;BLACK
CONTACT : COPPER ALLOY
SHELL : COPPER ALLOY
COIL : SWP
CAM ROD : SUS
HOOK SPRING : SUS

2 FINISH CONTACT : Ni UNDER PL
Au PL AT CONTACT AREA
SHELL : Ni UNDER PL
Au PL



△ NON-CUMULATIVE TOLERANCE
4. COPLANARITY IS 0.1MAX.
△ SWITCH MOVING AREA.
△ NO APPLIED TO WITHOUT BOSS TYPE.
△ CIRCUIT DRAWING OF SWITCH.




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.TSUJI 18NOV05		tyco Tyco Electronics AMP K.K.	
		CHK Y.NAKAZAWA 21NOV05		Electronics Kawasaki.Japan	
DIMENSIONS: 単位： 耗 MM		TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差		NAME 名称 MICRO SD WITH S/W PUSH PUSH STANDARD TYPE	
		APVD T.KUSUHARA 25NOV05		SIZE CAGE CODE DRAWING NO 番号 RESTRICTED TO	
		PRODUCT SPEC 製品規格			
		APPLICATION SPEC 取付適用規格			
MATERIAL 材料		FINISH 仕上		A300779C-1871602 —	
		WEIGHT		SCALE 尺度 5:1	
		CUSTOMER DRAWING		SHEET 1 OF 3 REV B	




PCB LAYOUT(REFERENCE)
(VIEWED FROM CONNECTOR MOUNT SIDE)
-1:WITHOUT BOSS TYPE



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN —	tyco Electronics Tyco Electronics AMP K.K. Kawasaki,Japan		
DIMENSIONS: 単位: 耗 MM		CHK —			
TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差		APVD —			
PRODUCT SPEC 製品規格		NAME 名称 MICRO SD WITH S/W PUSH PUSH STANDARD TYPE			
APPLICATION SPEC 取付適用規格		SIZE A3			
MATERIAL 材料		CAGE CODE 00779			
FINISH 仕上		DRAWING NO 番号 C-1871602			
WEIGHT		RESTRICTED TO —			
CUSTOMER DRAWING		SCALE 尺度 5:1			
		SHEET 2 OF 3			
		REV B			



PCB LAYOUT(REFERENCE)
(VIEWED FROM CONNECTOR MOUNT SIDE)
-2:WITH BOSS TYPE



剝離強度 1N MAX(300mm/min)
PEELING STRENGTH
剝離角度 165~180°
PEELING ANGLE

引き出し方向
TOP OF REEL

1000個/リール
1000EA/REEL

HOLE
86

空 部

	WITHOUT CHARGE	WITH PRODUCT CHARGE
1. Number of units sold	100	100
2. Selling price per unit	\$100	\$100
3. Variable cost per unit	\$60	\$70
4. Contribution margin per unit	\$40	\$30
5. Total contribution margin	\$4,000	\$3,000
6. Fixed costs	\$2,000	\$2,000
7. Operating income	\$2,000	\$1,000

空 部

WITHOUT CHARGE

300mm程度
APPROX

600mm程度
APPROX

REV	
-----	--