

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301050067](#)
Status: **Active**
Overview: [Specialty Lighting](#)
Description: Watertite Wet Location 60W Flood Light with In-line Transformer, Switch Screw Release Guard, 14/2 SOOW, Overall Length 7.62m (50.0')

Documents:
[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification	
CSA	LR85374
General	
Product Family	Portable Lighting
Series	130105
NEMA Configuration	NEMA 5-15
NEMA Rating	NEMA 4X
Outlet	None
Overview	Specialty Lighting
Product Name	Watertite
Type	Hand Lamps, Specialty Light
UPC	78678861575
Physical	
Cord Length - Primary	3.04m (10.0')
Cord Length - Secondary	15.24m (50.0')
Depth	N/A
Duty	Wet Location
Guard Included	Yes
Guard Type	Screw Release
Height	127.00mm (5.000")
Length	228.60mm (9.000")
Material - Guard	#10 Gauge Vinyl Coated Steel
Mounting Style	Hand Held
Packaging Type	Carton
Socket Construction	N/A
Electrical	
Bulb Type	Quartz Halogen
Cord Type - Primary	16/3 SOOW
Cord Type - Secondary	14/2 SOOW
Lamp Type	PAR36
Lamp Wattage - Maximum	60W
Lumens	600
On/Off Switch	Yes
Voltage (Fixture) - Maximum	120VAC 60 HZ
Voltage (Secondary) - Maximum	12V AC
Material Info	
Engineering Number	1692-12BS



Series image - Reference only

<u>EU ELV</u> Not Reviewed	
<u>EU RoHS</u> Not Reviewed	<u>China RoHS</u>
<u>REACH SVHC</u> Not Reviewed	
<u>Halogen-Free</u> <u>Status</u> Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[130105](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION