



GREENLEE®
A Textron Company

MADE FOR THE TRADE!™

CRIMPER 1300 NON-INSULATED AWG 22-12

TOOL WITH DIE



Image
Unavailable

Cat No: PA1306

UPC No: 769328100174

Description

TOOL WITH DIE

Specifications

- Cable Type : Open Barrel Non-Insulated Terminals, Narrow Lugs And Power Contacts
- Connection : Solid Or Stranded Wire, 22-10AWG (0.340 - 6.000 SQ-MM), F Type
- Crimping Range : 22-18/16-14/12-10 AWG (0.340 - 0.750/1.500 - 2.500/4.000 - 6.000 SQ-MM)