

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

FT

0

P

LTR

DESCRIPTION

DATE

DWN

APVD

B2

REVISED PER ECO-12-015027




21AUG2012

KH


MB

POLARIZATION KEY SLOT

CAVITY FOR M2.5 FIXING SCREW



284539-3 AS SHOWN



SQUARE NUT



MATERIALS AND FINISH

HOUSING : PA 6.6, UL 94-V0, COLOR GREEN

TERMINAL : PHOSPHOR BRONZE, TIN PLATED

SQUARE NUT-CuZn42 ALLOY

2

CONNECTOR ASSEMBLY INCLUDED 2 SQUARE NUTS
LOADED IN CAVITY.

3

SUITABLE FOR 1.6-2.4 mm. PC BOARD THICKNESS.



NOT CUMULATIVE TOLERANCE.

5


ADDITIONAL SQUQRE NUTS INCLUDED.

6

PACKAGED IN A BAG.

77.0	23	2-284539-3
73.5	22	2-284539-2
70.0	21	2-284539-1
66.5	20	2-284539-0
63.0	19	1-284539-9
59.5	18	1-284539-8
56.0	17	1-284539-7
52.5	16	1-284539-6
49.0	15	1-284539-5
45.5	14	1-284539-4
42.0	13	1-284539-3
38.5	12	1-284539-2
35.0	11	1-284539-1
31.5	10	1-284539-0
28.0	9	284539-9
24.5	8	284539-8
21.0	7	284539-7
17.5	6	284539-6
14.0	5	284539-5
10.5	4	284539-4
7.0	3	284539-3
3.5	2	284539-2
DIM A	NO OF POS	PART NUMBER


RECOMMENDED PC BOARD LAYOUT



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	±
1 PLC	±.3
2 PLC	±.25
3 PLC	±
4 PLC	±
ANGLES	±2

MATERIAL



FINISH



DWN

E. ZANOLINI

07FEB2002

CHK

E. ZANOLINI

07FEB2002

APVD

D. BIEVENOUR

07FEB2002

PRODUCT SPEC

108-20166

APPLICATION SPEC

114-20079

WEIGHT

-

Customer Drawing

TE

TE Connectivity

NAME

TERMINAL BLOCK, HEADER ASSEMBLY
90 DEG 3.5mm PITCH
WITH THREADED FLANGE

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A300779

C-284539

SCALE

3:1

SHEET

OF

REV

B2