

NOTES: UNLESS OTHERWISE SPECIFIED


1. CONSTRUCTION:

INSULATOR: P.V.C. AVAILABLE IN BLACK OR RED.
CONTACT: ANACONDA 7021 OR BOILCAT C97.
GOLD PLATED.
SOCKET: BRASS. TIN PLATED.

2. PERFORMANCE:

MAXIMUM CURRENT: 13 AMPS
MAXIMUM VOLTAGE: 300 V
MAXIMUM TEMPERATURE: 122°F (50°C)

REVISIONS		DESCRIPTION	DATE	APPROVED
LTR				



		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ANGLES ± .XX ± ± .XXX ±	CONTRACT NO.		E-Z-HOOK DIVISION OF TEKTEST INC. ARCADIA, CA 91006 U.S.A.				
			APPROVALS						DATE
			DRAWN	R.L.					3/09
			APPROVED BY						
		MATERIAL			DESCRIPTION E-Z-FLEX BAN SKT TO 0.062 [1.57] PIN ADAPTER (16AWG)				
		SEE NOTE.							
		FINISH							
		SEE NOTE.							
NEXT ASSY	USED ON				SIZE	CODE IDENT NO.	DRAWING NO.	REV.	
					A	08505	9340		
APPLICATION		DO NOT SCALE DRAWING			SCALE	2:1		SHEET 1 OF 1	